




Datasheet



-  - Temperature range
-10 ... +60°C
-  - Operating pressure
-0.1 ... 0.8 MPa



This indicator is activated when the pressure in a line is greater than 0.12 MPa.

It is designed for checking and indicating the operating status.

When activated, a coloured sleeve projects into the sight cap; this can be clearly seen from all sides thanks to the effective visualisation and an integrated reflecting surface.

General technical data

Pneumatic connection	Barbed connector PK-3
Product weight [g]	10

Operating and environmental conditions

Operating pressure	[MPa]	-0.1 ... 0.8
	[bar]	-1 ... 8
	[psi]	-14.5 ... 116
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]	
PWIS conformity	VDMA24364-B1/B2-L	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	-10 ... +60	

Materials

Note on materials	RoHS-compliant
-------------------	----------------

Ordering data

Pneumatic connection	Indicator colour	Part no.	Type
Barbed connector PK-3	Red	10088	OH-8-RT
	Green	10089	OH-8-GN
	Blue	10090	OH-8-BL
	Yellow	10091	OH-8-GE

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com

2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com

3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com

4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change