




Datasheet



-  - Temperature range
-10 ... +60°C
-  - Operating pressure
-0.1 ... 0.8 MPa



This indicator is activated when the pressure in a line is greater than 0.12 MPa.

It is designed for checking and indicating the operating status.

When activated, a coloured sleeve projects into the sight cap; this can be clearly seen from all sides thanks to the effective visualisation and an integrated reflecting surface.

General technical data

Pneumatic connection	Barbed connector PK-3
Product weight [g]	10

Operating and environmental conditions

Operating pressure	[MPa]	-0.1 ... 0.8
	[bar]	-1 ... 8
	[psi]	-14.5 ... 116
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]	
PWIS conformity	VDMA24364-B1/B2-L	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	-10 ... +60	

Materials

Note on materials	RoHS-compliant
-------------------	----------------

Ordering data

Pneumatic connection	Indicator colour	Part no.	Type
Barbed connector PK-3	Red	10088	OH-8-RT
	Green	10089	OH-8-GN
	Blue	10090	OH-8-BL
	Yellow	10091	OH-8-GE