



Datasheet



-  - Temperature range
-10 ... +80°C
-  - Operating pressure
0.14 ... 0.8 MPa



This indicator is activated when the pressure in a line is greater than 0.14 MPa.
It is designed for checking and indicating the operating status.

When activated, the indicator pointer projects by 3 mm and is clearly visible from all sides.

General technical data	
Pneumatic connection	Barbed connector PK-3
Product weight [g]	4

Operating and environmental conditions	
Operating pressure	[MPa] 0.14 ... 0.8
	[bar] 1.4 ... 8
	[psi] 20.3 ... 116
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]
PWIS conformity	VDMA24364-B1/B2-L
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature [°C]	-10 ... +80

Materials	
Note on materials	RoHS-compliant

Ordering data			
Pneumatic connection	Indicator colour	Part no.	Type
Barbed connector PK-3	Red	9791	OH-10