

Universal plug connectors NECU, for self-assembly

Technical data

Bus connection FBSD-KL

- Plug socket for fieldbus connection



General technical data	
Electrical connection	Angled socket, 5-pin; screw terminal, 5-pin
Operating voltage range [V DC]	24
Acceptable current load [A]	12
Connection cross section [mm ²]	0.2 ... 2.5
Type of mounting	2x M2.5x12 screws
Mounting position	Any
Protection class	IP20

Materials	
Pin contact	Gold-plated bronze
Housing	Polyamide (colour: black)

Operating and environmental conditions	
Ambient temperature [°C]	-5 ... +50
Storage temperature [°C]	-20 ... +70

Dimensions Download CAD data → www.festo.com

Ordering data			
Electrical connection	Weight [g]	Part No.	Type
Angled socket, 5-pin; screw terminal, 5-pin	20	525635	FBSD-KL-2x5POL

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change