

# Universal plug connectors NECU, for self-assembly

Technical data

Bus connection FBSD-KL

- Plug socket for fieldbus connection



General technical data	
Electrical connection	Angled socket, 5-pin; screw terminal, 5-pin
Operating voltage range [V DC]	24
Acceptable current load [A]	12
Connection cross section [mm <sup>2</sup> ]	0.2 ... 2.5
Type of mounting	2x M2.5x12 screws
Mounting position	Any
Protection class	IP20

Materials	
Pin contact	Gold-plated bronze
Housing	Polyamide (colour: black)

Operating and environmental conditions	
Ambient temperature [°C]	-5 ... +50
Storage temperature [°C]	-20 ... +70

**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)

Ordering data			
Electrical connection	Weight [g]	Part No.	Type
Angled socket, 5-pin; screw terminal, 5-pin	20	525635	FBSD-KL-2x5POL

# Festo - Your Partner in Automation



**1 Festo Inc.**  
 5300 Explorer Drive  
 Mississauga, ON L4W 5G4  
 Canada

**Festo Customer Interaction Center**  
 Tel: 1 877 463 3786  
 Fax: 1 877 393 3786  
 Email: [customer.service.ca@festo.com](mailto:customer.service.ca@festo.com)



**2 Festo Pneumatic**  
 Av. Ceylán 3,  
 Col. Tequesquináhuac  
 54020 Tlalnepantla,  
 Estado de México

**Multinational Contact Center**  
 01 800 337 8669  
[ventas.mexico@festo.com](mailto:ventas.mexico@festo.com)



**3 Festo Corporation**  
 1377 Motor Parkway  
 Suite 310  
 Islandia, NY 11749

**Festo Customer Interaction Center**  
 1 800 993 3786  
 1 800 963 3786  
[customer.service.us@festo.com](mailto:customer.service.us@festo.com)



**4 Regional Service Center**  
 7777 Columbia Road  
 Mason, OH 45040

Connect with us



[www.festo.com/socialmedia](http://www.festo.com/socialmedia)



[www.festo.com](http://www.festo.com)

Subject to change