




## Datasheet



-  - Temperature range  
-10 ... +80°C
-  - Operating pressure  
0.14 ... 0.8 MPa



This indicator is activated when the pressure in a line is greater than 0.14 MPa.

It is designed for checking and indicating the operating status.

When activated, the indicator pointer projects by 3 mm and is clearly visible from all sides.

| General technical data                 |                  |  |              |
|--|------------------|--|--------------|
| Pneumatic connection                   |                  | Barbed connector PK-3  |              |
| Product weight                         | [g]              | 4  |              |
| Operating and environmental conditions |                  |  |              |
| Operating pressure                     | [MPa]            | 0.14 ... 0.8   |              |
|  | [bar]            | 1.4 ... 8  |              |
|  | [psi]            | 20.3 ... 116   |              |
| Operating medium                       |                  | Compressed air to ISO 8573-1:2010 [7:::]   |              |
| PWIS conformity                        |                  | VDMA24364-B1/B2-L  |              |
| Note on the operating/pilot medium     |                  | Lubricated operation possible (in which case lubricated operation will always be required) |              |
| Ambient temperature                    | [°C]             | -10 ... +80  |              |
| Materials                              |                  |  |              |
| Note on materials                      |                  | RoHS-compliant   |              |
| Ordering data                          |                  |  |              |
| Pneumatic connection                   | Indicator colour | Part no.   | Type         |
| Barbed connector PK-3                  | Red              | <b>9791</b>  | <b>OH-10</b> |

# Festo - Your Partner in Automation



**1 Festo Inc.**  
5300 Explorer Drive  
Mississauga, ON L4W 5G4  
Canada

**Festo Customer Interaction Center**  
Tel: 1 877 463 3786  
Fax: 1 877 393 3786  
Email: [customer.service.ca@festo.com](mailto:customer.service.ca@festo.com)



**2 Festo Pneumatic**  
Av. Ceylán 3,  
Col. Tequesquináhuac  
54020 Tlalnepantla,  
Estado de México

**Multinational Contact Center**  
01 800 337 8669  
[ventas.mexico@festo.com](mailto:ventas.mexico@festo.com)



**3 Festo Corporation**  
1377 Motor Parkway  
Suite 310  
Islandia, NY 11749

**Festo Customer Interaction Center**  
1 800 993 3786  
1 800 963 3786  
[customer.service.us@festo.com](mailto:customer.service.us@festo.com)



**4 Regional Service Center**  
7777 Columbia Road  
Mason, OH 45040

Connect with us



[www.festo.com/socialmedia](http://www.festo.com/socialmedia)



[www.festo.com](http://www.festo.com)

Subject to change