




Datasheet



-  - Temperature range
-10 ... +80°C
-  - Operating pressure
0.14 ... 0.8 MPa



This indicator is activated when the pressure in a line is greater than 0.14 MPa.

It is designed for checking and indicating the operating status.

When activated, the indicator pointer projects by 3 mm and is clearly visible from all sides.

General technical data			
Pneumatic connection		Barbed connector PK-3	
Product weight	[g]	4	
Operating and environmental conditions			
Operating pressure	[MPa]	0.14 ... 0.8	
	[bar]	1.4 ... 8	
	[psi]	20.3 ... 116	
Operating medium		Compressed air to ISO 8573-1:2010 [7:::]	
PWIS conformity		VDMA24364-B1/B2-L	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature	[°C]	-10 ... +80	
Materials			
Note on materials		RoHS-compliant	
Ordering data			
Pneumatic connection	Indicator colour	Part no.	Type
Barbed connector PK-3	Red	9791	OH-10

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com

2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com

3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com

4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change