




Datasheet



-  - Temperature range
-10 ... +80°C
-  - Operating pressure
0.14 ... 0.8 MPa



This indicator is activated when the pressure in a line is greater than 0.14 MPa.

It is designed for checking and indicating the operating status.

When activated, the indicator pointer projects by 3 mm and is clearly visible from all sides.

General technical data			
Pneumatic connection		Barbed connector PK-3	
Product weight	[g]	4	
Operating and environmental conditions			
Operating pressure	[MPa]	0.14 ... 0.8	
	[bar]	1.4 ... 8	
	[psi]	20.3 ... 116	
Operating medium		Compressed air to ISO 8573-1:2010 [7:::]	
PWIS conformity		VDMA24364-B1/B2-L	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature	[°C]	-10 ... +80	
Materials			
Note on materials		RoHS-compliant	
Ordering data			
Pneumatic connection	Indicator colour	Part no.	Type
Barbed connector PK-3	Red	9791	OH-10