Multiple distributor QSLV, QST, QSQ

Characteristics

At a glance

Rotatable compressed air branches in the riser pipe principle. With single outlets.

Series

[QSQ] Multiple distributor, straight form, 4 outlets QSQ



[QSLV2] Multiple distributor, L-shape, 2 outlets QSLV2



[QSLV3] Multiple distributor, L-shape, 3 outlets QSLV3



[QSLV4] Multiple distributor, L-shape, 4 outlets QSLV4



[QSLV6] Multiple distributor, L-shape, 6 outlets QSLV6



[QST3] Multiple distributor, T-shape, 3 outlets QST3



[QSYTF] Multiple distributor QSYTF



Type code

001	Series	
QSLV2	Multiple distributor, L-shape, 2 outlets QSLV2	
QSLV3	Multiple distributor, L-shape, 3 outlets QSLV3	
QSLV4	Multiple distributor, L-shape, 4 outlets QSLV4	
QSLV6	Multiple distributor, L-shape, 6 outlets QSLV6	
QST3	Multiple distributor, T-shape, 3 outlets QST3	
QSQ	Multiple distributor, straight form, 4 outlets QSQ	

002	Pneumatic connection 1	
1/8	Male thread R1/8	
1/4	Male thread R1/4	
3/8	Male thread R3/8	
1/2	Male thread R1/2	
6	Push-in connector 6 mm	
8	Push-in connector 8 mm	
10	Push-in connector 10 mm	
G1/8	Male thread G1/8	
G1/4	Male thread G1/4	
G3/8	Male thread G3/8	
G1/2	Male thread G1/2	

003	Pneumatic connection 2	
4	Push-in connector 4 mm	
6	Push-in connector 6 mm	
8	Push-in connector 8 mm	
10	Push-in connector 10 mm	
12	Push-in connector 12 mm	

004	System of units	
	Metric	

Datasheet

General technical data

Size	Standard
Design	Push-pull principle
Mounting position	optional
Type of seal on screwed plug[1)]	Coating, Sealing ring
Size of pack	1

1) Sealing ring (G thread), coating (R thread)

Operating and environmental conditions

Operating pressure complete temperature range	-0.95 ... 6 bar
Temperature-dependent operating pressure	-0.95 ... 14 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Note on operating and pilot medium	Lubricated operation possible, Water: G-thread only possible with sealing ring type OL as additional accessory
Ambient temperature	-10 ... 80°C
Corrosion resistance class CRC [1)]	1 - Low corrosion stress
Maritime classification [2)]	See certificate

1) More information www.festo.com/x/topic/crc

2) More information www.festo.com/catalogue/qs → Support/Downloads

Operating pressure p as a function of temperature t



Materials

Material housing	PBT
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel
Material hollow bolt [1)]	Nickel-plated brass
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

1) QSLV

Tightening torques

Pneumatic connection, port 1	Male thread G1/8	Male thread G1/4	Male thread G3/8	Male thread G1/2	Male thread R1/8	Male thread R1/4	Male thread R3/8	Male thread R1/2
Nominal torque	5.4 ... 7 Nm	9 Nm	15.5 Nm	26 Nm	7 Nm	9 Nm	15.5 Nm	26 Nm
Tolerance for nominal tightening torque	± 20%							

Datasheet

Tubing insertion depth					
Pneumatic connection, port 2	For tubing outside diameter of 4 mm	For tubing outside diameter of 6 mm	For tubing outside diameter of 8 mm	For tubing outside diameter of 10 mm	For tubing outer diameter of 12 mm
Tubing insertion depth	15 mm	17 mm	18.1 mm	20.2 mm	23.4 mm

Dimensions

Dimensions – Multiple distributor QSQ, R thread Download CAD data www.festo.com



	D1	D2	B1	D5 ø	L1	L2	L4	⫧
QSQ-1/8-4	R1/8	4	10,3	10,5	38,9	8	34,9	12
QSQ-1/8-6		6	12,5	13	47,2	8	43,2	12
QSQ-1/4-4	R1/4	4	10,3	10,5	42,4	11	36,4	14
QSQ-1/4-6		6	12,5	13	50,7	11	44,7	14

Dimensions

Dimensions – Multiple distributor QSQ, G thread with sealing ring Download CAD data www.festo.com



[1] Sealing ring

	D1	D2	B1	D5 ø	L1	L2	L6	⫷
QSQ-G1/8-4	R1/8	4	10,3	10,5	37	4,2	1,9	13
QSQ-G1/8-6		6	12,5	13	45,3	4,2	1,9	13
QSQ-G1/4-4	R1/4	4	10,3	10,5	39,1	4,8	1,9	17
QSQ-G1/4-6		6	12,5	13	47,4	4,8	1,9	17

Dimensions

Dimensions – Multiple distributor QSQ, reducing

Download CAD data www.festo.com



	D1	D2	B1	D5 ø	D6 ø	D7 ø	L1	L2
QSQ-6-4	6	4	10,3	10,5	3,2	12,5	37,5	14,2
QSQ-8-6	8	6	12,5	13	3,2	14,5	42	15,8

Dimensions

Dimensions – Multiple distributor QSLV2, R thread Download CAD data www.festo.com



	D1	D2	D5 ø	H1	H2	H3	H4	H5	L1	⫷1
QSLV2-1/8-4	R1/8	4	10	41,6	8	15,5	13	37,6	22,2	14
QSLV2-1/8-6		6	12,5	41,6	8	15,5	13	37,6	24,2	14
QSLV2-1/8-8		8	14,5	46,6	8	17,5	15	42,6	27,7	17
QSLV2-1/4-6	R1/4	6	12,5	44,6	11	16,5	13	38,6	24,2	14
QSLV2-1/4-8		8	14,5	49,6	11	18,5	15	43,6	27,7	17
QSLV2-1/4-10		10	17,5	57,6	11	22	18	51,6	31,7	22
QSLV2-3/8-8	R3/8	8	14,5	50,6	12	19,2	15	44,3	27,7	17
QSLV2-3/8-10		10	17,5	58,6	12	22,7	18	52,3	31,7	22
QSLV2-3/8-12		12	21	68,8	12	27,5	21,6	62,5	36,7	27
QSLV2-1/2-12	R1/2	12	21	71,8	15	28,6	21,6	63,6	36,7	27

Dimensions

Dimensions – Multiple distributor QSLV2, G thread with sealing ring Download CAD data www.festo.com



	D1	D2	D5 ø	H1	H2	H3	H4	L1	⫧1
QSLV2-G1/8-4	G1/8	4	10	40,6	5,1	13,4	13	22,2	14
QSLV2-G1/8-6		6	12,5	40,6	5,1	13,4	13	24,2	14
QSLV2-G1/8-8		8	14,5	45,6	5,1	15,4	15	27,7	17
QSLV2-G1/4-6	G1/4	6	12,5	42,1	5,6	14,4	13	24,2	17
QSLV2-G1/4-8		8	14,5	46,1	5,6	15,4	15	27,7	17
QSLV2-G1/4-10		10	17,5	54,1	5,6	18,9	18	31,7	22
QSLV2-G3/8-8	G3/8	8	14,5	47,6	6,6	15,9	15	27,7	19
QSLV2-G3/8-10		10	17,5	55,6	6,6	19,4	18	31,7	22
QSLV2-G3/8-12		12	21	65,8	6,6	24,2	21,6	36,7	27
QSLV2-G1/2-12	G1/2	12	21	66,8	7,6	24,2	21,6	36,7	27

Dimensions

Dimensions – Multiple distributor QSLV3, R thread

Download CAD data www.festo.com



	D1	D2	D5 ø	H1	H2	H3	H4	H5	L1	⇔1
QSLV3-1/8-4	R1/8	4	10	54,7	8	15,5	13	50,7	22,2	14
QSLV3-1/8-6		6	12,5	54,7	8	15,5	13	50,7	24,2	14
QSLV3-1/8-8		8	14,5	61,7	8	17,5	15	57,7	27,7	17
QSLV3-1/4-6	R1/4	6	12,5	57,7	11	16,5	13	51,7	24,2	14
QSLV3-1/4-8		8	14,5	64,7	11	18,5	15	58,7	27,7	17
QSLV3-1/4-10		10	17,5	75,7	11	22	18	69,7	31,7	22
QSLV3-3/8-8	R3/8	8	14,5	65,7	12	19,2	15	59,4	27,7	17
QSLV3-3/8-10		10	17,5	76,7	12	22,7	18	70,4	31,7	22
QSLV3-3/8-12		12	21	90,5	12	27,5	21,6	84,2	36,7	27
QSLV3-1/2-12	R1/2	12	21	93,5	15	28,6	21,6	85,3	36,7	27

Dimensions

Dimensions – Multiple distributor QSLV3, G thread with sealing ring Download CAD data www.festo.com



	D1	D2	D5 ø	H1	H2	H3	H4	L1	⫰1
QSLV3-G1/8-4	G1/8	4	10	53,7	5,1	13,4	13	22,2	14
QSLV3-G1/8-6		6	12,5	53,7	5,1	13,4	13	24,2	14
QSLV3-G1/8-8		8	14,5	60,7	5,1	15,4	15	27,7	17
QSLV3-G1/4-6	G1/4	6	12,5	55,2	5,6	14,4	13	24,2	17
QSLV3-G1/4-8		8	14,5	61,2	5,6	15,4	15	27,7	17
QSLV3-G1/4-10		10	17,5	72,2	5,6	18,9	18	31,7	22
QSLV3-G3/8-8	G3/8	8	14,5	62,7	6,6	15,9	15	27,7	19
QSLV3-G3/8-10		10	17,5	73,3	6,6	19,4	18	31,7	22
QSLV3-G3/8-12		12	21	87,5	6,6	24,2	21,6	36,7	27
QSLV3-G1/2-12	G1/2	12	21	88,5	7,6	24,2	21,6	36,7	27

Dimensions

Dimensions – Multiple distributor QSLV4, R thread

Download CAD data www.festo.com



	D1	D2	D5 ø	H1	H2	H3	H4	H5	L1	B1	⫧1
QSLV4-1/8-4	R1/8	4	10	41,6	8	15,5	13	37,6	22,2	10	14
QSLV4-1/8-6		6	12,5	41,6	8	15,5	13	37,6	24,2	12	14
QSLV4-1/8-8		8	14,5	46,6	8	17,5	15	42,6	27,7	14	17
QSLV4-1/4-6	R1/4	6	12,5	44,6	11	16,5	13	38,6	24,2	12	14
QSLV4-1/4-8		8	14,5	49,6	11	18,5	15	43,6	27,7	14	17
QSLV4-1/4-10		10	17,5	57,6	11	22	18	51,6	31,7	17	22
QSLV4-3/8-8	R3/8	8	14,5	50,6	12	19,2	15	44,3	27,7	14	17
QSLV4-3/8-10		10	17,5	58,6	12	22,7	18	52,3	31,7	17	22
QSLV4-3/8-12		12	21	68,8	12	27,5	21,6	62,5	36,7	20	27
QSLV4-1/2-12	R1/2	12	21	71,8	15	28,6	21,6	63,6	36,7	20	27

Dimensions

Dimensions – Multiple distributor QSLV4, G thread with sealing ring Download CAD data www.festo.com





	D1	D2	D5 ø	H1	H2	H3	H4	L1	B1	⫷1
QSLV4-G1/8-4	R1/8	4	10	40,6	5,1	13,4	13	22,2	10	14
QSLV4-G1/8-6		6	12,5	40,6	5,1	13,4	13	24,2	12	14
QSLV4-G1/8-8		8	14,5	45,6	5,1	15,4	15	27,7	14	17
QSLV4-G1/4-6	R1/4	6	12,5	42,1	5,6	14,4	13	24,2	12	17
QSLV4-G1/4-8		8	14,5	46,1	5,6	15,4	15	27,7	14	17
QSLV4-G1/4-10		10	17,5	54,1	5,6	18,9	18	31,7	17	22
QSLV4-G3/8-8	R3/8	8	14,5	47,6	6,6	15,9	15	27,7	14	19
QSLV4-G3/8-10		10	17,5	55,6	6,6	19,4	18	31,7	17	22
QSLV4-G3/8-12		12	21	65,8	6,6	24,2	21,6	36,7	20	27
QSLV4-G1/2-12	R1/2	12	21	66,8	7,6	24,2	21,6	36,7	20	27

Dimensions

Dimensions – Multiple distributor QSLV6, R thread

Download CAD data www.festo.com



	D1	D2	D5 ø	H1	H2	H3	H4	H5	L1	B1	⫧1
QSLV6-1/8-4	R1/8	4	10	54,7	8	15,5	13	50,7	22,2	10	14
QSLV6-1/8-6		6	12,5	54,7	8	15,5	13	50,7	24,2	12	14
QSLV6-1/8-8		8	14,5	61,7	8	17,5	15	57,7	27,7	14	17
QSLV6-1/4-6	R1/4	6	12,5	57,7	11	16,5	13	51,7	24,2	12	14
QSLV6-1/4-8		8	14,5	64,7	11	18,5	15	58,7	27,7	14	17
QSLV6-1/4-10		10	17,5	75,7	11	22	18	69,7	31,7	17	22
QSLV6-3/8-8	R3/8	8	14,5	65,7	12	19,2	15	59,4	27,7	14	17
QSLV6-3/8-10		10	17,5	76,7	12	22,7	18	70,4	31,7	17	22
QSLV6-3/8-12		12	21	90,5	12	27,5	21,6	84,2	36,7	20	27
QSLV6-1/2-12	R1/2	12	21	93,5	15	28,6	21,6	85,3	36,7	20	27

Dimensions

Dimensions – Multiple distributor QSLV6, G thread with sealing ring Download CAD data www.festo.com



	D1	D2	D5 ø	H1	H2	H3	H4	L1	B1	⫧1
QSLV6-G1/8-4	G1/8	4	10	53,7	5,1	13,4	13	22,2	10	14
QSLV6-G1/8-6		6	12,5	53,7	5,1	13,4	13	24,2	12	14
QSLV6-G1/8-8		8	14,5	60,7	5,1	15,4	15	27,7	14	17
QSLV6-G1/4-6	G1/4	6	12,5	55,2	5,6	14,4	13	24,2	12	17
QSLV6-G1/4-8		8	14,5	61,2	5,6	15,4	15	27,7	14	17
QSLV6-G1/4-10		10	17,5	72,2	5,6	18,9	18	31,7	17	22
QSLV6-G3/8-8	G3/8	8	14,5	62,7	6,6	15,9	15	27,7	14	19
QSLV6-G3/8-10		10	17,5	73,7	6,6	19,4	18	31,7	17	22
QSLV6-G3/8-12		12	21	87,5	6,6	24,2	21,6	36,7	20	27
QSLV6-G1/2-12	G1/2	12	21	88,5	7,6	24,2	21,6	36,7	20	27

Dimensions

Dimensions – Multiple distributor QST3, R thread Download CAD data www.festo.com



	D1	D2	D3	D5 ø	D7 ø	H1	L1	L2	L3	L5	⬡
QST3-1/8-6-4	R1/8	6	4	12,5	10	18,4	65,4	8	61,4	20	12
QST3-1/4-8-6	R1/4	8	6	14,5	12,5	21,3	76,9	11	70,9	25	14
QST3-3/8-10-8	R3/8	10	8	17,5	14,5	23,7	87,8	12	81,5	29	17

Dimensions

Dimensions – Multiple distributor QST3, G thread with sealing ring

Download CAD data www.festo.com



	D1	D2	D3	D5 ø	D7 ø	H1	L1	L2	L5	L6	⫧
QST3-G1/8-6-4	G1/8	6	4	12,5	10	18,4	63,5	4,2	20	1,9	13
QST3-G1/4-8-6	G1/4	8	6	14,5	12,5	21,3	73,6	4,8	25	1,9	17
QST3-G3/8-10-8	G3/8	10	8	17,5	14,5	23,7	84	5,8	29	2,4	19

Dimensions

Dimensions – Multiple distributor QST3, reducing

Download CAD data www.festo.com



	D1	D2	D3	D5 ø	D6 ø	D7 ø	H1	H2	L1	L4	L5
QST3-6-4	6	6	4	13	3,3	10	18,5	8	60	34	20
QST3-8-6	8	8	6	15	3,3	13	21	9	69,5	40	24
QST3-10-8	10	10	8	18	3,3	15	23,5	10,5	80	46	28

Dimensions

Dimensions – Multiple distributor QSYTF, R thread Download CAD data www.festo.com





	D1	D2	B1	D3 ø	D5 ø	D6 ø	H1	H2	H3	H4	L1	L2	⌀
QSYTF-1/8-6-B	R1/8	6	12	G1/8	12,4	3,5	32,5	8	12	7	26,2	10,7	14
QSYTF-1/4-8-B	R1/4	8	14	G1/4	14,4	3,2	38,5	11	13,5	9	29,1	12,5	17
QSYTF-3/8-10-B	R3/8	10	17	G3/8	17,6	4,2	44,5	12	15,7	11	33,5	15	21
QSYTF-1/2-12-B	R1/2	12	20	G1/2	21	4,2	52,2	13	16,5	14	37,4	17	24

Dimensions

Dimensions – Multiple distributor QSYTF, G thread with sealing ring

Download CAD data www.festo.com



	D1	D2	B1	D3 ø	D5 ø	D6 ø	H1	H2	H3	H4	L1	L2	⫧
QSYTF-G1/8-6	G1/8	6	12	G1/8	12,4	3,2	29,2	5,1	15,2	7	27,5	12	17
QSYTF-G1/4-8	G1/4	8	14	G1/4	14,4	3,2	32,9	5,6	16,4	9	30,9	14	19
QSYTF-G3/8-10	G3/8	10	17	G3/8	17,6	4,2	41,4	6,6	19,4	11	34	15,5	21
QSYTF-G1/2-12	G1/2	12	20	G1/2	21	4,2	47,4	7,6	21,9	14	38,9	18,5	27

Ordering data

Multiple distributor QSQ

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G1/8	For tubing outside diameter of 4 mm	2.6 mm	20 g	**186220**	**QSQ-G1/8-4**
		For tubing outside diameter of 6 mm	5.2 mm	26 g	**186222**	**QSQ-G1/8-6**
	Male thread G1/4	For tubing outside diameter of 4 mm	2.6 mm	29 g	**186221**	**QSQ-G1/4-4**
		For tubing outside diameter of 6 mm	5.2 mm	35 g	**186263**	**QSQ-G1/4-6**
	Male thread R1/8	For tubing outside diameter of 4 mm	2.6 mm	16 g	**153206**	**QSQ-1/8-4**
		For tubing outside diameter of 6 mm	5.2 mm	25 g	**153208**	**QSQ-1/8-6**
	Male thread R1/4	For tubing outside diameter of 4 mm	2.6 mm	21 g	**153207**	**QSQ-1/4-4**
		For tubing outside diameter of 6 mm	5.2 mm	30 g	**153288**	**QSQ-1/4-6**
	For tubing outside diameter of 6 mm	For tubing outside diameter of 4 mm	3.1 mm	14 g	★ **153209**	**QSQ-6-4**
	For tubing outer diameter of 8 mm	For tubing outside diameter of 6 mm	4.6 mm	21 g	★ **153210**	**QSQ-8-6**

Multiple distributor QSLV2

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G1/8	For tubing outside diameter of 4 mm	2.4 mm	25 g	**186223**	**QSLV2-G1/8-4**
		For tubing outside diameter of 6 mm	3.2 mm	27 g	★ **186224**	**QSLV2-G1/8-6**
		For tubing outside diameter of 8 mm	4.2 mm	43 g	**186226**	**QSLV2-G1/8-8**
	Male thread G1/4	For tubing outside diameter of 6 mm	3.2 mm	36 g	**186225**	**QSLV2-G1/4-6**
		For tubing outside diameter of 8 mm	4.3 mm	44 g	★ **186227**	**QSLV2-G1/4-8**
		For tubing outside diameter of 10 mm	5.2 mm	77 g	**186229**	**QSLV2-G1/4-10**
	Male thread G3/8	For tubing outside diameter of 8 mm	4.3 mm	53 g	**186228**	**QSLV2-G3/8-8**
		For tubing outside diameter of 10 mm	5.3 mm	79 g	**186230**	**QSLV2-G3/8-10**

Ordering data

Multiple distributor QSLV2

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G3/8	For tubing outer diameter of 12 mm	6.3 mm	135 g	**186231**	**QSLV2-G3/8-12**
	Male thread G1/2		6.4 mm	140 g	**186232**	**QSLV2-G1/2-12**
	Male thread R1/8	For tubing outside diameter of 4 mm	2.4 mm	26 g	**153211**	**QSLV2-1/8-4**
		For tubing outside diameter of 6 mm	3.2 mm	28 g	★ **153212**	**QSLV2-1/8-6**
		For tubing outside diameter of 8 mm	4.2 mm	44 g	**153214**	**QSLV2-1/8-8**
	Male thread R1/4	For tubing outside diameter of 6 mm	3.2 mm	34 g	★ **153213**	**QSLV2-1/4-6**
		For tubing outside diameter of 8 mm	4.3 mm	47 g	★ **153215**	**QSLV2-1/4-8**
		For tubing outside diameter of 10 mm	5.2 mm	80 g	★ **153217**	**QSLV2-1/4-10**
	Male thread R3/8	For tubing outside diameter of 8 mm	4.3 mm	54 g	**153216**	**QSLV2-3/8-8**
		For tubing outside diameter of 10 mm	5.3 mm	83 g	**153218**	**QSLV2-3/8-10**
	Male thread R1/2	For tubing outer diameter of 12 mm	6.3 mm	139 g	**153219**	**QSLV2-3/8-12**
			6.4 mm	149 g	**153220**	**QSLV2-1/2-12**

Multiple distributor QSLV3

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G1/8	For tubing outside diameter of 4 mm	2.4 mm	32 g	**186233**	**QSLV3-G1/8-4**
		For tubing outside diameter of 6 mm	3.2 mm	35 g	**186234**	**QSLV3-G1/8-6**
		For tubing outside diameter of 8 mm	4.3 mm	55 g	**186236**	**QSLV3-G1/8-8**
	Male thread G1/4	For tubing outside diameter of 6 mm	3.2 mm	43 g	**186235**	**QSLV3-G1/4-6**
		For tubing outside diameter of 8 mm	4.2 mm	56 g	**186237**	**QSLV3-G1/4-8**
		For tubing outside diameter of 10 mm	5.2 mm	96 g	**186239**	**QSLV3-G1/4-10**
	Male thread G3/8	For tubing outside diameter of 8 mm	4.3 mm	65 g	**186238**	**QSLV3-G3/8-8**
		For tubing outside diameter of 10 mm	5.3 mm	98 g	**186240**	**QSLV3-G3/8-10**

Ordering data

Multiple distributor QSLV3

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G3/8	For tubing outer diameter of 12 mm	6.4 mm	167 g	**186241**	**QSLV3-G3/8-12**
	Male thread G1/2		6.5 mm	171 g	**186242**	**QSLV3-G1/2-12**
	Male thread R1/8	For tubing outside diameter of 4 mm	2.4 mm	33 g	**153221**	**QSLV3-1/8-4**
		For tubing outside diameter of 6 mm	3.2 mm	35 g	**153222**	**QSLV3-1/8-6**
		For tubing outside diameter of 8 mm	4.3 mm	56 g	**153224**	**QSLV3-1/8-8**
	Male thread R1/4	For tubing outside diameter of 6 mm	3.2 mm	41 g	**153223**	**QSLV3-1/4-6**
		For tubing outside diameter of 8 mm	4.2 mm	59 g	**153225**	**QSLV3-1/4-8**
		For tubing outside diameter of 10 mm	5.2 mm	99 g	**153227**	**QSLV3-1/4-10**
	Male thread R3/8	For tubing outside diameter of 8 mm	4.3 mm	66 g	**153226**	**QSLV3-3/8-8**
		For tubing outside diameter of 10 mm	5.3 mm	102 g	**153228**	**QSLV3-3/8-10**
		For tubing outer diameter of 12 mm	6.4 mm	171 g	**153229**	**QSLV3-3/8-12**
	Male thread R1/2		6.5 mm	180 g	**153230**	**QSLV3-1/2-12**

Multiple distributor QSLV4

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G1/8	For tubing outside diameter of 4 mm	2.3 mm	30 g	**186243**	**QSLV4-G1/8-4**
		For tubing outside diameter of 6 mm	2.9 mm	34 g	**186244**	**QSLV4-G1/8-6**
		For tubing outside diameter of 8 mm	4 mm	53 g	**186246**	**QSLV4-G1/8-8**
	Male thread G1/4	For tubing outside diameter of 6 mm	2.9 mm	42 g	**186245**	**QSLV4-G1/4-6**
		For tubing outside diameter of 8 mm	4.1 mm	54 g	**186247**	**QSLV4-G1/4-8**
		For tubing outside diameter of 10 mm	5 mm	92 g	**186249**	**QSLV4-G1/4-10**
	Male thread G3/8	For tubing outside diameter of 8 mm	4.1 mm	63 g	**186248**	**QSLV4-G3/8-8**
		For tubing outside diameter of 10 mm	5.1 mm	94 g	**186250**	**QSLV4-G3/8-10**

Ordering data

Multiple distributor QSLV4

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G3/8	For tubing outer diameter of 12 mm	6 mm	158 g	**186251**	**QSLV4-G3/8-12**
	Male thread G1/2		6.2 mm	162 g	**186252**	**QSLV4-G1/2-12**
	Male thread R1/8	For tubing outside diameter of 4 mm	2.3 mm	31 g	**153231**	**QSLV4-1/8-4**
		For tubing outside diameter of 6 mm	2.9 mm	35 g	**153232**	**QSLV4-1/8-6**
		For tubing outside diameter of 8 mm	4 mm	54 g	**153234**	**QSLV4-1/8-8**
	Male thread R1/4	For tubing outside diameter of 6 mm	2.9 mm	40 g	**153233**	**QSLV4-1/4-6**
		For tubing outside diameter of 8 mm	4.1 mm	56 g	**153235**	**QSLV4-1/4-8**
		For tubing outside diameter of 10 mm	5 mm	95 g	**153237**	**QSLV4-1/4-10**
	Male thread R3/8	For tubing outside diameter of 8 mm	4.1 mm	64 g	**153236**	**QSLV4-3/8-8**
		For tubing outside diameter of 10 mm	5.1 mm	98 g	**153238**	**QSLV4-3/8-10**
		For tubing outer diameter of 12 mm	6 mm	162 g	**153239**	**QSLV4-3/8-12**
	Male thread R1/2		6.2 mm	171 g	**153240**	**QSLV4-1/2-12**

Multiple distributor QSLV6

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G1/8	For tubing outside diameter of 4 mm	2.3 mm	39 g	**186253**	**QSLV6-G1/8-4**
		For tubing outside diameter of 6 mm	2.9 mm	45 g	**186254**	**QSLV6-G1/8-6**
		For tubing outside diameter of 8 mm	4 mm	70 g	**186256**	**QSLV6-G1/8-8**
	Male thread G1/4	For tubing outside diameter of 6 mm	2.9 mm	53 g	**186255**	**QSLV6-G1/4-6**
		For tubing outside diameter of 8 mm	4 mm	71 g	**186257**	**QSLV6-G1/4-8**
		For tubing outside diameter of 10 mm	5.2 mm	119 g	**186259**	**QSLV6-G1/4-10**
	Male thread G3/8	For tubing outside diameter of 8 mm	4.1 mm	80 g	**186258**	**QSLV6-G3/8-8**
		For tubing outside diameter of 10 mm	5.2 mm	122 g	**186260**	**QSLV6-G3/8-10**

Ordering data

Multiple distributor QSLV6

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G3/8	For tubing outer diameter of 12 mm	6.3 mm	201 g	**186261**	**QSLV6-G3/8-12**
	Male thread G1/2			205 g	**186262**	**QSLV6-G1/2-12**
	Male thread R1/8	For tubing outside diameter of 4 mm	2.3 mm	40 g	**153241**	**QSLV6-1/8-4**
		For tubing outside diameter of 6 mm	2.9 mm	45 g	**153242**	**QSLV6-1/8-6**
		For tubing outside diameter of 8 mm	4 mm	71 g	**153244**	**QSLV6-1/8-8**
	Male thread R1/4	For tubing outside diameter of 6 mm	2.9 mm	51 g	**153243**	**QSLV6-1/4-6**
		For tubing outside diameter of 8 mm	4 mm	73 g	★ **153245**	**QSLV6-1/4-8**
		For tubing outside diameter of 10 mm	5.2 mm	122 g	**153247**	**QSLV6-1/4-10**
	Male thread R3/8	For tubing outside diameter of 8 mm	4.1 mm	81 g	**153246**	**QSLV6-3/8-8**
		For tubing outside diameter of 10 mm	5.2 mm	126 g	**153248**	**QSLV6-3/8-10**
	Male thread R1/2	For tubing outer diameter of 12 mm	6.3 mm	205 g	**153249**	**QSLV6-3/8-12**
				214 g	**153250**	**QSLV6-1/2-12**

Multiple distributor QST3

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G1/8	For tubing outside diameter of 4 mm, For tubing outside diameter of 6 mm	3 mm	21 g	**186217**	**QST3-G1/8-6-4**
	Male thread G1/4	For tubing outside diameter of 6 mm, For tubing outside diameter of 8 mm	4.6 mm	35 g	**186218**	**QST3-G1/4-8-6**
	Male thread G3/8	For tubing outside diameter of 8 mm, For tubing outside diameter of 10 mm	6.7 mm	52 g	**186219**	**QST3-G3/8-10-8**
	Male thread R1/8	For tubing outside diameter of 4 mm, For tubing outside diameter of 6 mm	3 mm	21 g	**153200**	**QST3-1/8-6-4**
	Male thread R1/4	For tubing outside diameter of 6 mm, For tubing outside diameter of 8 mm	4.6 mm	35 g	**153201**	**QST3-1/4-8-6**

Ordering data

Multiple distributor QST3

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread R3/8	For tubing outside diameter of 8 mm, For tubing outside diameter of 10 mm	6.7 mm	50 g	**153202**	**QST3-3/8-10-8**
	For tubing outside diameter of 6 mm	For tubing outside diameter of 4 mm	2.5 mm	16 g	★ **153203**	**QST3-6-4**
	For tubing outer diameter of 8 mm	For tubing outside diameter of 6 mm	3.6 mm	23 g	★ **153204**	**QST3-8-6**
	For tubing outer diameter of 10 mm	For tubing outside diameter of 8 mm	4.9 mm	33 g	★ **153205**	**QST3-10-8**

Multiple distributor QSYTF

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Product weight	Part no.	Type
	Male thread G1/8	Female thread G1/8, For tubing outside diameter of 6 mm	3.1 mm	32 g	**186213**	**QSYTF-G1/8-6**
	Male thread G1/4	Female thread G1/4, For tubing outside diameter of 8 mm	4.3 mm	47 g	**186214**	**QSYTF-G1/4-8**
	Male thread G3/8	Female thread G3/8, For tubing outside diameter of 10 mm	5.5 mm	72 g	**186215**	**QSYTF-G3/8-10**
	Male thread G1/2	Female thread G1/2, For tubing outer diameter of 12 mm	6.8 mm	127 g	**186216**	**QSYTF-G1/2-12**
	Male thread R1/8	Female thread G1/8, For tubing outside diameter of 6 mm	4.2 mm	27 g	**153196**	**QSYTF-1/8-6-B**
	Male thread R1/4	Female thread G1/4, For tubing outside diameter of 8 mm	6 mm	44 g	**153197**	**QSYTF-1/4-8-B**
	Male thread R3/8	Female thread G3/8, For tubing outside diameter of 10 mm	8 mm	73 g	**153198**	**QSYTF-3/8-10-B**
	Male thread R1/2	Female thread G1/2, For tubing outer diameter of 12 mm	10 mm	110 g	**153199**	**QSYTF-1/2-12-B**