










































[→ Catalogue](#)[→ 2D/3D view](#)[→ Spare parts catalogue](#)

| 8073100 VTSA-F-CB (Valve terminal) | | | | | | | | |
|------------------------------------|--|----------|---|---|------|------|---|--|
| Pos. | IC IC designation | Part no. | | Type Article designation Hint | Qty. | Unit | Order | |
| 1 | 51E CPX-M - Modular electrical terminal, metal interlinking | 550212 |  | CPX-M-EPL-EV End plate | 1 | PC |  | |
| 2 | F33 Fieldbus node for PROFINET IO, 2 x M12, metal design | 548755 |  | CPX-FB33 Bus node | 1 | PC |  | |
| 3 | QP Connecting block with system supply, 7/8", 5-pin | 550208 |  | CPX-M-GE-EV-S-7/8-5POL Interlinking block | 1 | PC |  | |
| 4 | RC CPX pneumatic interface with serial communication to VTSA-CB, with 3 secure zones (PROFIsafe) | 8068240 | | VABA-S6-1-X2-F1-CB Pneumatic interface | 1 | PC |  | |
| 5 | Y Pilot air selector | 539238 |  | VABE-S6-1RZ-G-B1 End plate | 1 | PC |  | |
| 6 | CB Blanking plug | 3569 |  | B-1/4 Blanking plug | 1 | PC |  | |
| 7 | U Additional supply plate and exhaust plate (0 addresses) | 8092506 | | VABF-S6-1-P1A7-G12-CB Supply plate | 1 | PC |  | |
| 8 | YB Manifold sub-base for switchable pilot air with second valve position, size 18 mm (2 addresses) | 8068913 | | VABV-S4-2HS-G18-CB-2T5 Manifold sub-base | 1 | PC |  | |
| 9 | A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses) | 8067932 | | VABV-S4-2HS-G18-CB-2T2 Manifold sub-base | 1 | PC |  | |
| 10 | L Duct separation 14 | 573191 |  | VABD-S6-1-P7-C Channel separation | 1 | PC |  | |
| 11 | USW Additional supply plate and exhaust plate with address extension (24 addresses), for safe voltage zone | 8104044 | | VABF-S6-1-P8A7-G12-CB1 Extension module | 1 | PC |  | |
| 12 | YC Manifold sub-base for switchable pilot air with second valve position, size 26 mm (2 addresses) | 8068912 | | VABV-S4-12HS-G-CB-2T5 Manifold sub-base | 1 | PC |  | |
| 13 | B Manifold sub-base for size 26 mm, 2 valve positions (4 addresses) | 8067940 | | VABV-S4-1HS-G14-CB-2T2 Manifold sub-base | 1 | PC |  | |
| 14 | CS 3/2-way pilot air switching valve, internal pilot air supply via duct 1 of the end plate/additional supply plate | 8066569 | | VSVA-BT-M32CS1-MYE-A2-1T5L-PA Solenoid valve | 1 | PC |  | |
| 15 | -" | 3568 |  | B-1/8 Blanking plug | 1 | PC |  | |
| 16 | -" | 1205860 |  | AMTE-M-LH-G18 Silencer | 1 | PC |  | |
| 17 | J 5/2-way valve, bistable | 8033450 |  | VSVA-B-B52-ZTR-A2-1T1L Solenoid valve | 1 | PC |  | |
| 18 | L Vacant position | 539213 |  | VABB-S4-2-WT Cover plate | 1 | PC |  | |
| 19 | L Vacant position | 539213 |  | VABB-S4-2-WT Cover plate | 1 | PC |  | |
| 20 | CS 3/2-way pilot air switching valve, internal pilot air supply via duct 1 of the end plate/additional supply plate | 8066569 | | VSVA-BT-M32CS1-MYE-A2-1T5L-PA Solenoid valve | 1 | PC |  | |
| 21 | -" | 3568 |  | B-1/8 Blanking plug | 1 | PC |  | |
| 22 | -" | 1205860 |  | AMTE-M-LH-G18 Silencer | 1 | PC |  | |
| 23 | J 5/2-way valve, bistable | 8033019 |  | VSVA-B-B52-ZTR-A1-1T1L Solenoid valve | 1 | PC |  | |

8073100 VTSA-F-CB (Valve terminal) — Series: All

51E-F33GCQP-RC

46P-B-YZCB-UYLNGWOGWYBAYQLUSWYLNWOGWYCB-CSJLLCSJLL

| 8073100 VTSA-F-CB (Valve terminal) | | | | | | | |
|------------------------------------|----------------------|----------|---|-------------------------------------|------|------|---|
| Pos. | IC IC designation | Part no. | | Type Article designation Hint | Qty. | Unit | Order |
| 24 | L Vacant position | 539212 |  | VABB-S4-1-WT Cover plate | 1 | PC |  |
| 25 | L Vacant position | 539212 |  | VABB-S4-1-WT Cover plate | 1 | PC |  |