



































[→ Catalogue](#)[→ 2D/3D view](#)[→ Spare parts catalogue](#)





















8073100 VTSA-F-CB (Valve terminal)								
Pos.	IC IC designation	Part no.		Type Article designation Hint	Qty.	Unit	Order	
1	51E CPX-M - Modular electrical terminal, metal interlinking	550212		CPX-M-EPL-EV End plate	1	PC		
2	F36 Fieldbus node for Ethernet/IP or Modbus TCP, 2 x M12	1912451		CPX-FB36 Bus node	1	PC		
3	QP Connecting block with system supply, 7/8", 5-pin	550208		CPX-M-GE-EV-S-7/8-5POL Interlinking block	1	PC		
4	RB CPX pneumatic interface with serial communication to VTSA-CB, with 3 external power supplies for the zones	8082878		VABA-S6-1-X2-3V-CB Pneumatic interface	1	PC		
5	Y Pilot air selector	539238		VABE-S6-1RZ-G-B1 End plate	1	PC		
6	- "-	3569		B-1/4 Blanking plug	1	PC		
7	PV Soft-start valve (0 addresses)	8068609		VABV-S6-1Q-G38-CB1-T5 Manifold sub-base	1	PC		
8	PN Soft-start valve, without pilot air provision, with exhaust, duct 3/5	8067405		VABF-S6-1-P5A4S2YE-G12-1T5-PA Soft start valve	1	PC		
9	YB Manifold sub-base for switchable pilot air with second valve position, size 18 mm (2 addresses)	8068913		VABV-S4-2HS-G18-CB-2T5 Manifold sub-base	1	PC		
10	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC		
11	L Duct separation 14	573191		VABD-S6-1-P7-C Channel separation	1	PC		
12	USW Additional supply plate and exhaust plate with address extension (24 addresses), for safe voltage zone	8104044		VABF-S6-1-P8A7-G12-CB1 Extension module	1	PC		
13	NBS Blanking plug	3571		B-1/2 Blanking plug	1	PC		
14	YC Manifold sub-base for switchable pilot air with second valve position, size 26 mm (2 addresses)	8068912		VABV-S4-12HS-G-CB-2T5 Manifold sub-base	1	PC		
15	B Manifold sub-base for size 26 mm, 2 valve positions (4 addresses)	8067940		VABV-S4-1HS-G14-CB-2T2 Manifold sub-base	1	PC		
16	TL Duct separation 1/14	8060483		VABD-S6-1-P8-C Channel separation	1	PC		
17	UW Additional supply plate and exhaust plate with address extension (24 addresses), for unsafe voltage zone	8104042		VABF-S6-1-P8A7-G12-CB Extension module	1	PC		
18	A Manifold sub-base for size 18 mm, 2 valve positions (4 addresses)	8067932		VABV-S4-2HS-G18-CB-2T2 Manifold sub-base	1	PC		
19	III 2 mm high negative pressure	8067140		VABF-S4-2-V2B1-G38-CB-VH-20-A Vacuum generator	1	PC		
20	ZQA Sturdy non-detenting, detenting via accessories	4105147		VAMC-B-S6-CTR Cover cap	2	PC		
21	CS 3/2-way pilot air switching valve, internal pilot air supply via duct 1 of the end plate/additional supply plate	8066569		VSVA-BT-M32CS1-MYE-A2-1T5L-PA Solenoid valve	1	PC		
22	- "-	3568		B-1/8 Blanking plug	1	PC		
23	- "-	1205860		AMTE-M-LH-G18 Silencer	1	PC		

8073100 VTSA-F-CB (Valve terminal) — Series: All

51E-F36GCQP-RB

46P-B-YS-

PVPNNGWOGWZQZYBAYQLUSWYLNBSOGWYCBYQTLUWYLNWOGWAQIIIZQA-
CSJLLCSJLLJL

8073100 VTSA-F-CB (Valve terminal)							
Pos.	IC IC designation	Part no.		Type Article designation Hint	Qty.	Unit	Order
24	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
25	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
26	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	
27	CS 3/2-way pilot air switching valve, internal pilot air supply via duct 1 of the end plate/additional supply plate	8066569		VSVA-BT-M32CS1-MYE-A2-1T5L-PA Solenoid valve	1	PC	
28	-"	3568		B-1/8 Blanking plug	1	PC	
29	-"	1205860		AMTE-M-LH-G18 Silencer	1	PC	
30	J 5/2-way valve, bistable	8033019		VSVA-B-B52-ZTR-A1-1T1L Solenoid valve	1	PC	
31	L Vacant position	539212		VABB-S4-1-WT Cover plate	1	PC	
32	L Vacant position	539212		VABB-S4-1-WT Cover plate	1	PC	
33	J 5/2-way valve, bistable	8033450		VSVA-B-B52-ZTR-A2-1T1L Solenoid valve	1	PC	
34	L Vacant position	539213		VABB-S4-2-WT Cover plate	1	PC	