

# Pressure indicator OH-8-RT

Part number: 10088

FESTO



## Data sheet

Feature	Value
Operating pressure	-0.1 MPa...0.8 MPa -1 bar...8 bar -14.5 psi...116 psi
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Pneumatic connection	Barbed fitting PK-3
Note on materials	RoHS-compliant