

Elbow quick connector LCK-1/4-PK-9

Part number: 11452

FESTO



Data sheet

Feature	Value
Nominal size	8 mm
Type of seal on screwed plug	Sealing ring
Mounting position	optional
Design	L-shape
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Nominal torque	11 Nm
Tolerance for nominal tightening torque	± 10%
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	For barbed fitting inside diameter of 9 mm with nut
Material union nut	Wrought aluminium alloy, anodised
Note on materials	RoHS-compliant
Material sealing ring	Reinforced PA TPE-U(PU)
Material hollow bolt	Wrought aluminium alloy, anodised
Material swivel fitting	Die-cast zinc