


Limit switch attachments

SRBF-CA6-YR90-MW-22A-C2M20

Part number: 1152498

FESTO

With mounting adapter, 30x130 mm hole pattern, for drives with 50 mm shaft height.



Data sheet

Feature	Value
Design	Angular
Based on the standard	EN 60947-5-1 ISO 5211
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Materials note	Contains PWIS substances Conforms to RoHS
Measuring principle	Mechanical/electrical For proximity sensor
Ambient temperature	-25 ... 80 °C
Switching element function	Changeover switch
Max. contact rating AC	1,770 VA
Max. contact rating DC	36 W
Operating voltage range AC	0 ... 250 V
Operating voltage range DC	0 ... 24 V
Connectable nominal conductor cross section	0.5 ... 1.5 mm ²
Mounting type	On flange to ISO 5211 with accessories
Assembly position	Any
Product weight	725 g
Materials information, housing	Aluminium die cast Painted
Material information, accessories supplied	High alloy steel High alloy steel, non-corrosive
Setting range, angle recording	0 ... 90 deg
Protection class	IP67
Insulation voltage	250 V
Surge strength	4 kV
Corrosion resistance classification CRC	0
Degree of contamination	3