

Check valve
H-1/2-B
Part number: 11691

FESTO



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Type of mounting	Screw-in
Operating pressure	0.04 MPa...1.2 MPa 0.4 bar...12 bar
Ambient temperature	-10 °C...60 °C
Material housing	Anodised wrought aluminium alloy
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Mounting position	optional
Standard nominal flow rate 1->2 (6-5)	5500 l/min
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C...60 °C
Media temperature	-10 °C...60 °C
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Max. tightening torque	40 Nm
Product weight	58.3 g
Note on materials	RoHS-compliant
Material seals	NBR