

Throttle plate GRO-ZP-3-ISO

Part number: 119674



Data sheet

| Feature | Value |
|---|--|
| Valve function | Flow control function |
| Operating pressure | 0 bar...16 bar |
| Standard nominal flow rate (standardised to DIN 1343) | 1500 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:...] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Media temperature | -20 °C...80 °C |
| Ambient temperature | -20 °C...80 °C |
| Type of mounting | With through-hole |