

# Plastic tubing PU-13-SW

Part number: 12133

FESTO



## Data sheet

Feature	Value
Outside diameter	17.6 mm
Flow-relevant bending radius	83 mm
Inside diameter	13 mm
Operating pressure complete temperature range	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-35 °C...60 °C
Product weight according to length	0.133 kg/m
Pneumatic connection	For barbed fitting inside diameter of 13 mm with union nut
Colour	Black
Shore hardness	A 86 +/-3
Note on materials	RoHS-compliant
Material tubing	TPE-U(PU)