

Cartridge QSPLKG14-5/16-U

Part number: 132941

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	4.8 mm
Mounting position	optional
Design	L-shape Push-pull principle
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Maritime classification	See certificate
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...60 °C 23 °F...140 °F
Product weight	7.1 g
Type of mounting	Mounting pin
Pneumatic connection, port 1	Cartridge 14 mm
Pneumatic connection, port 2	For tubing outside diameter of 5/16"
Colour of release ring	grey
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel