

Blanking plug QSMC-2H

Part number: 133036

FESTO



Data sheet

Feature	Value
Size	Mini
Mounting position	optional
Design	Blanking plug
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa...0.6 MPa -0.95 bar...6 bar -13.775 psi...87 psi
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...80 °C
Product weight	0.1 g
Pneumatic connection, port 1	Push-in sleeve Ø 2 mm
Note on materials	RoHS-compliant
Material housing	PBT