

Push-in T-fitting NPQP-T-R12-Q12-FD

Part number: 133080

FESTO



Data sheet

| Feature | Value |
|--|---|
| Size | Standard |
| Nominal size | 6.9 mm |
| Design | T-shape Push-pull principle |
| Size of pack | 1 |
| Temperature-dependent operating pressure | -0.95 bar...10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:...] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 4 - Very high corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Suitable for use with food | See supplementary material information |
| Ambient temperature | -20 °C...60 °C |
| Product weight | 28 g |
| Type of mounting | External hexagon, size 22 mm |
| Pneumatic connection, port 1 | Male thread R1/2 |
| Pneumatic connection, port 2 | For tubing outer diameter of 12 mm |
| Note on materials | RoHS-compliant |
| Material housing | PP |
| Material tubing clamp component | High-alloy stainless steel |