

Push-in bulkhead connector NPQP-H-Q4-E-FD

Part number: 133100

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	2.3 mm
Design	Bulkhead Push-pull principle
Size of pack	1
Temperature-dependent operating pressure	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:...]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C...60 °C
Product weight	7.2 g
Pneumatic connection, port 1	For tubing outer diameter of 4 mm
Pneumatic connection, port 2	For tubing outside diameter of 4 mm
Note on materials	RoHS-compliant
Material housing	PP
Material nut	High-alloy stainless steel
Material tubing clamp component	High-alloy stainless steel