

# Push-in connector NPQP-D-Q4-S6-FD-P10

Part number: 133133

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal size	2.5 mm
Design	Straight design Push-pull principle
Size of pack	10
Temperature-dependent operating pressure	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:...]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C...60 °C
Product weight	2.4 g
Pneumatic connection, port 1	Push-in sleeve Ø 6 mm
Pneumatic connection, port 2	For tubing outside diameter of 4 mm
Note on materials	RoHS-compliant
Material housing	PP
Material tubing clamp component	High-alloy stainless steel