

# Push-in L-fitting NPQP-L-R38-Q10-FD

Part number: 133165

**FESTO**



## Data sheet

| Feature                                  | Value                                     |
|--|---|
| Size                                     | Standard                                  |
| Nominal size                             | 5.7 mm                                    |
| Design                                   | L-shape<br>Push-pull principle            |
| Size of pack                             | 1   |
| Temperature-dependent operating pressure | -0.95 bar...10 bar                        |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:...] |
| Note on operating and pilot medium       | Lubricated operation possible             |
| Corrosion resistance class CRC           | 4 - Very high corrosion stress            |
| LABS (PWIS) conformity                   | VDMA24364 zone III                        |
| Suitable for use with food               | See supplementary material information    |
| Ambient temperature                      | -20 °C...60 °C                            |
| Product weight                           | 13 g                                      |
| Type of mounting                         | External hexagon, size 17 mm              |
| Pneumatic connection, port 1             | Male thread R3/8                          |
| Pneumatic connection, port 2             | For tubing outside diameter of 10 mm      |
| Note on materials                        | RoHS-compliant                            |
| Material housing                         | PP  |
| Material tubing clamp component          | High-alloy stainless steel                |