

Push-in connector NPQP-D-Q8-Q6-FD

Part number: 133168

FESTO



Data sheet

| Feature | Value |
|--|---|
| Size | Standard |
| Nominal size | 4.3 mm |
| Design | Straight design Push-pull principle |
| Size of pack | 1 |
| Temperature-dependent operating pressure | -0.95 bar...10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:...] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 4 - Very high corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Suitable for use with food | See supplementary material information |
| Ambient temperature | -20 °C...60 °C |
| Product weight | 7 g |
| Pneumatic connection, port 1 | For tubing outer diameter of 8 mm |
| Pneumatic connection, port 2 | For tubing outside diameter of 6 mm |
| Note on materials | RoHS-compliant |
| Material housing | PP |
| Material tubing clamp component | High-alloy stainless steel |