


Shut-off valve HE-2-1/4-QS-8

Part number: 153472

FESTO



Data sheet

Feature	Value
Valve function	2/2 double solenoid
Pneumatic connection, port 1	R1/4
Pneumatic connection, port 2	QS-8
Type of actuation	Manual
Type of mounting	Direct mounting via through-hole Direct mounting via thread Either:
Standard nominal flow rate (standardised to DIN 1343)	423.9 l/min
Nominal size	3.5 mm
Operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar
Ambient temperature	0 °C...60 °C
Material housing	PBT-reinforced
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]
Sealing principle	Soft
Mounting position	optional
Design	Piston gate valve
Type of piloting	Direct
Flow direction	Reversible
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 4 according to ISO 14644-1
Media temperature	0 °C...60 °C
Product weight	36 g
Material screwed plug	Nickel-plated brass
Note on materials	RoHS-compliant
Material seals	NBR