

Clamping sleeve
EAMH-110-20-C34-P
Part number: 1545246



Data sheet

Feature	Value
Size	110
Mounting position	optional
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	30.2 kgmm ²
Product weight	217 g
Note on materials	RoHS-compliant