

# Swivel flange SUA-50

Part number: 157324

FESTO



## Data sheet

| Feature                        | Value                            |
|--------------------------------|----------------------------------|
| Size                           | 50                               |
| Mounting position              | optional                         |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress    |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                |
| Ambient temperature            | -40 °C...90 °C                   |
| Product weight                 | 288 g                            |
| Note on materials              | RoHS-compliant                   |
| Material mounting              | Wrought aluminium alloy          |
| Material bolt                  | Galvanised steel                 |
| Material sleeve                | Spring steel                     |
| Material bearing               | Polymer                          |
| Material screws                | Galvanised steel                 |
| Material lock                  | Spring steel                     |
| Material shaft                 | Steel<br>With protective coating |