

Barbed fitting CN-M3-PK-2

Part number: 15871

FESTO



Data sheet

Feature	Value
Nominal size	1.5 mm
Type of seal on screwed plug	Sealing ring
Operating pressure complete temperature range	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:...]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C...60 °C
Pneumatic connection, port 1	Male thread M3
Pneumatic connection, port 2	For tubing outer diameter of 3 mm
Note on materials	RoHS-compliant
Material housing	High-alloy steel