

Push-in connector QS-V0-12

Part number: 160549

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal size | 11 mm |
| Fire test material | UL94 V-0 (housing) UL94 V-0 (releasing ring) |
| Design | Straight design Push-pull principle |
| Size of pack | 1 |
| Operating pressure complete temperature range | -0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi |
| Note on operating pressure | Water: max. 0.6 MPa at max. 50°C |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:::] Water (liquid, ice-free) |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C...60 °C |
| Product weight | 25 g |
| Pneumatic connection, port 1 | For tubing outer diameter of 12 mm |
| Pneumatic connection, port 2 | For tubing outer diameter of 12 mm |
| Colour of release ring | Black |
| Note on materials | RoHS-compliant |
| Material housing | PBT |
| Material release ring | PBT |
| Material tubing seal | NBR |
| Material tubing clamp component | High-alloy stainless steel Brass |