

Flange mounting

CRFNG-63

Part number: 161849

FESTO



Data sheet

Feature	Value
Size	63
Mounting position	optional
Conforms to standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	680 g
Material mounting	High-alloy stainless steel
Material screws	High-alloy stainless steel