

Foot mounting CRHBN-20/25X1

Part number: 161867

FESTO



Data sheet

Feature	Value
Size	20/25
Mounting position	optional
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Product weight	94 g
Note on materials	RoHS-compliant
Material mounting	High-alloy stainless steel
Material nut	High-alloy steel