

**Sub-base**  
**PAML-CP-186-HP3-G114**  
Part number: 1629296

**FESTO**



**Data sheet**

| Feature                        | Value                                    |
|--------------------------------|------------------------------------------|
| Size                           | 186                                      |
| Nominal size DN                | 54                                       |
| Series                         | L                                        |
| Operating pressure             | 0 MPa...5 MPa<br>0 bar...50 bar          |
| Operating medium               | Compressed air to ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress            |
| LABS (PWIS) conformity         | VDMA24364-B2-L                           |
| Storage temperature            | -10 °C...60 °C                           |
| Suitable for use with food     | See supplementary material information   |
| Media temperature              | 5 °C...60 °C                             |
| Ambient temperature            | 5 °C...60 °C                             |
| Product weight                 | 4600 g                                   |
| Pneumatic connection, port 1   | G1 1/4                                   |
| Pneumatic connection, port 2   | G1 1/4                                   |
| Note on materials              | RoHS-compliant                           |
| Material sub-base              | Wrought aluminium alloy                  |
| Material seals                 | NBR                                      |
| Material screws                | Stainless steel                          |