

Sub-base
PAML-CP-186-HP3-G112
Part number: 1629297

FESTO



Data sheet

Feature	Value
Size	186
Nominal size DN	54
Series	L
Operating pressure	0 MPa...5 MPa 0 bar...50 bar
Operating medium	Compressed air to ISO 8573-1:2010 [:-:-]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C...60 °C
Suitable for use with food	See supplementary material information
Media temperature	5 °C...60 °C
Ambient temperature	5 °C...60 °C
Product weight	4500 g
Pneumatic connection, port 1	G1 1/2
Pneumatic connection, port 2	G1 1/2
Note on materials	RoHS-compliant
Material sub-base	Wrought aluminium alloy
Material seals	NBR
Material screws	Stainless steel