

# Foot mounting CRH-50

Part number: 162953

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Size   | 50   |
| Mounting position                                  | optional   |
| Corrosion resistance class CRC                     | 4 - Very high corrosion stress   |
| LABS (PWIS) conformity                             | VDMA24364-B1/B2-L  |
| Suitability for the production of Li-ion batteries | Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Product weight                                     | 916 g  |
| Note on materials                                  | RoHS-compliant   |
| Material mounting                                  | High-alloy stainless steel   |
| Material nut                                       | High-alloy steel   |