

Manifold block CPE18-PRSE-2

Part number: 164972

FESTO



Data sheet

| Feature | Value |
|------------------------------------|--|
| Max. number of valve positions | 2 |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 145 g |
| Mounting method for sub-base | With through-hole With H-rail |
| Pneumatic connection, port 1 | G1/2 |
| Note on materials | RoHS-compliant |
| Material housing | PA-reinforced |