

Plug socket with cable KMEB-2-24-2,5-LED

Part number: 174844

FESTO



Data sheet

Feature	Value
Switching position indicator	LED
Type of mounting	On solenoid valve via M2.5 central screw
Mounting position	optional
Product weight	200 g
Electrical connection	4-pin Angled socket Type C To DIN EN 175301-803
Nominal operating voltage DC	24 V
Protective conductor connection	Available
Cable length	2.5 m
Cable diameter	6.2 mm
Cable structure	3 x 0.75 mm ²
Degree of protection	IP65 To IEC 60529
Ambient temperature	-20 °C...80 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material cable sheath	TPE-U(PUR)
Material housing	PA POM
Material electrical contact	Bronze