

Plug socket with cable

KMEB-2-230-5

Part number: 174847

FESTO



Data sheet

Feature	Value
Type of mounting	On solenoid valve via M2.5 central screw
Mounting position	optional
Product weight	400 g
Electrical connection	4-pin Angled socket Type C To DIN EN 175301-803
Nominal operating voltage AC	230 V
Protective conductor connection	Available
Cable length	5 m
Cable diameter	6.2 mm
Cable structure	3 x 0.75 mm ²
Degree of protection	IP65 To IEC 60529
Ambient temperature	-20 °C...80 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material cable sheath	TPE-U(PUR)
Material housing	PA POM
Material electrical contact	Bronze