

Push-in T-connector CQT-18-15

Part number: 177699

FESTO



Data sheet

Feature	Value
Nominal size	12 mm
Mounting position	optional
Size of pack	1
Design	Push-pull principle
Operating pressure complete temperature range	-0.95 bar...7 bar
Temperature-dependent operating pressure	-0.95 bar...15 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-25 °C...70 °C
Product weight	42 g
Number of outputs	2
Number of supply lines	1
Pneumatic connection, port 1	For pipe/tubing outside diameter of 18 mm
Pneumatic connection, port 2	For pipe/tubing outside diameter of 15 mm
Note on materials	RoHS-compliant
Material housing	POM
Material release ring	POM
Material tubing clamp component	High-alloy stainless steel