

# Plug socket FBSD-GD-13,5

Part number: 18496

**FESTO**



## Data sheet

Feature	Value
Based on standard	EN 61076-2-101 EN 61984
Type of mounting	Via union nut
Mounting position	optional
Product weight	40 g
Electrical connection	4-pin Straight socket/screw terminal Type A M12x1
Operational voltage range DC	250 V
Operational voltage range AC	250 V
Current rating at 40° C	4 A
Immunity to surge	2.5 kV
Cable fitting	Pg 13.5
Permissible cable diameter	10 mm...12 mm
Connection cross section	0.75 mm <sup>2</sup>
Degree of protection	IP67
Ambient temperature	-40 °C...85 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Pollution degree	3
Corrosion resistance class CRC	1 - Low corrosion stress
Material housing	PA-reinforced
Housing colour	Black
Material union nut	Die-cast zinc Nickel-plated
Material electrical contact	Bronze White bronze coated