

Multiple distributor QSLV4-G1/4-8

Part number: 186247

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal size | 4.1 mm |
| Type of seal on screwed plug | Sealing ring |
| Mounting position | optional |
| Design | Push-pull principle |
| Size of pack | 1 |
| Operating pressure complete temperature range | -0.095 MPa...0.6 MPa -0.95 bar...6 bar -13.775 psi...87 psi |
| Temperature-dependent operating pressure | -0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi |
| Note on operating pressure | Water: max. 0.6 MPa at 0 - 50 °C |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) |
| Note on operating and pilot medium | Lubricated operation possible Water: G-thread only possible with sealing ring type OL as additional accessory |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C...80 °C |
| Nominal torque | 9 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 54 g |
| Number of outputs | 4 |
| Number of supply lines | 1 |
| Pneumatic connection, port 1 | Male thread G1/4 |
| Pneumatic connection, port 2 | For tubing outside diameter of 8 mm |
| Colour of release ring | Blue |
| Note on materials | RoHS-compliant |
| Material housing | PBT |
| Material hollow bolt | Nickel-plated brass |
| Material release ring | POM |

| Feature | Value |
|---------------------------------|----------------------------|
| Material tubing seal | NBR |
| Material tubing clamp component | High-alloy stainless steel |