


manifold block VIGK-04-D-3-NPT

Part number: 18889

FESTO

For valve terminal

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

Feature	Value
Operating pressure	-0.9 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-:]
Authorisation	UL - Recognized (OL)
Materials note	Conforms to RoHS