

Suction gripper ESG-4

Part number: 189168



Data sheet

Feature	Value
Suction cup diameter	4 mm
Mounting position	Vertical
Special characteristics	Antistatic
Design	Vacuum port on top Vacuum port on side With height compensator With long height compensator
Correlation to suction-cup holder	Size 1
Suction cup shape	Round, flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-30 °C...200 °C
Vacuum connection	M3 M10x1 QS-4 PK-3
Note on materials	RoHS-compliant
Material suction cup	BR FPM NBR PUR VMQ (silicone)