

Suction gripper ESG-30

Part number: 189174

FESTO



Data sheet

Feature	Value
Suction cup diameter	30 mm
Mounting position	Vertical
Special characteristics	Antistatic
Design	Vacuum port on top Vacuum port on side With height compensator With long height compensator
Correlation to suction-cup holder	Size 4
Suction cup shape	Round bellows 1.5 convolutions Round bellows 3.5 convolutions Round extra deep Round, flat Round deep
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-30 °C...200 °C
Vacuum connection	M14x1 G1/8 QS-6 PK-4
Note on materials	RoHS-compliant
Material suction cup	BR FPM NBR PUR VMQ (silicone) Vulkollan