

# Suction gripper ESG-200

Part number: 189181

FESTO



## Data sheet

Feature	Value
Suction cup diameter	200 mm
Mounting position	Vertical
Design	Vacuum port on top Vacuum port on side With height compensator With long height compensator
Correlation to suction-cup holder	Size 6
Suction cup shape	Round, flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-30 °C...200 °C
Vacuum connection	G1/4
Note on materials	RoHS-compliant
Material suction cup	FPM NBR PUR VMQ (silicone)