

Suction gripper ESG-6X20

Part number: 189185

FESTO



Data sheet

| Feature | Value |
|-----------------------------------|--|
| Suction cup size | 6x20 mm |
| Mounting position | Vertical |
| Design | Vacuum port on top Vacuum port on side With height compensator With long height compensator |
| Correlation to suction-cup holder | Size 4 |
| Suction cup shape | Oval, flat |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| Ambient temperature | -10 °C...70 °C |
| Vacuum connection | M14x1 G1/8 QS-6 PK-4 |
| Note on materials | RoHS-compliant |
| Material suction cup | NBR |