

# Suction cup complete holder ESH-HF-1-M10X1

Part number: 189260

**FESTO**



## Data sheet

Feature	Value
Height compensator for suction-cup holder	2.6 mm
Nominal size	2 mm
Volume	0.108 cm <sup>3</sup>
Mounting position	Vertical
Design	Vacuum port on top With height compensator
Correlation to suction-cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	14 g
Type of mounting	Via male thread Via vacuum port
Suction cup mounting	Diameter 3 mm
Vacuum connection	M10x1
Note on materials	RoHS-compliant
Material seals	NBR POM
Material retaining bracket	Tempered steel