

# Suction cup complete ESS-40-EN

Part number: 189346

**FESTO**



## Data sheet

Feature	Value
Min. workpiece radius	80 mm
Nominal size	3 mm
Suction cup diameter	40 mm
Suction cup volume	4.04 cm <sup>3</sup>
Position of connection	Top
Mounting position	optional
Correlation to suction-cup holder	Size 4
Suction cup shape	Round extra deep
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Suitable for use with food	See supplementary material information
Ambient temperature	-10 °C...70 °C
Holding force at nominal operating pressure	67.6 N
Lateral force at nominal operating pressure	53 N
Product weight	16.9 g
Type of mounting	Via vacuum port
Vacuum connection	M6
Colour	Black
Shore hardness	60 +/- 5
Material screwed plug	Nickel-plated wrought aluminium alloy Nickel-plated brass Steel, galvanised and chrome-plated
Note on materials	RoHS-compliant
Material suction cup	NBR