

# Multiple distributor QSLV4-1/4-1/4-U

Part number: 190793

**FESTO**



## Data sheet

Feature	Value
Size	Standard
Nominal size	3.1 mm
Type of seal on screwed plug	Coating
Mounting position	optional
Design	Push-pull principle
Size of pack	1
Operating pressure complete temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Maritime classification	See certificate
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C 14 °F...140 °F
Max. tightening torque	14 Nm
Product weight	40 g
Number of outputs	4
Number of supply lines	1
Pneumatic connection, port 1	Male thread 1/4 NPT
Pneumatic connection, port 2	For tubing outside diameter of 1/4"
Colour of release ring	grey
Material screwed plug	Nickel-plated brass
Note on materials	RoHS-compliant
Material housing	PBT
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel