

Check valve H-QSM-3/16-U Part number: 190842

FESTO



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	QS-3/16
Pneumatic connection, port 2	QS-5/16
Type of mounting	In-line installation
Standard nominal flow rate (standardised to DIN 1343)	189 l/min
Operating pressure	-1 bar...10 bar
Ambient temperature	0 °C...60 °C
Material housing	Aluminium
Operating medium	Compressed air to ISO 8573-1:2010 [7:~:]
Min. diff. pressure, opening	0.1 bar
Min. diff. pressure, closing	0.2 bar
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	10 g
Note on materials	RoHS-compliant