

Check valve
HA-1/4-QS-5/16-U
 Part number: 190854

FESTO



Data sheet

| Feature | Value |
|---|--|
| Valve function | Non-return function |
| Pneumatic connection, port 1 | 1/4 NPT |
| Pneumatic connection, port 2 | QS-5/16 |
| Type of mounting | Screw-in |
| Standard nominal flow rate (standardised to DIN 1343) | 766 l/min |
| Operating pressure | -1 bar...10 bar |
| Ambient temperature | 0 °C...60 °C |
| Material housing | Brass |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:~:] |
| Min. diff. pressure, opening | 0.1 bar |
| Min. diff. pressure, closing | 0.2 bar |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 24 g |
| Note on materials | RoHS-compliant |